



Powering Business Worldwide

pe.eaton.com

General-Purpose Transformer, Ventilated

T27M11S15EE

UPC:786685197456

Dimensions:

- **Height:** 31.3 IN
- **Length:** 18.39 IN
- **Width:** 22.89 IN

Weight:242 LB

Notes:NEMA TP-1 efficient

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Dry Type Distribution Transformer
- **Design:** DS-3
- **Coil Material:** Aluminum windings
- **Frame:** 816
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 277V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 15 KVA
- **Weathershield:** WS11

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - T27M11S15EE](#)

Certifications:

- UL Listed



Product compliance:

- NEMA TP-1 Compliant

© 2016 Eaton. All rights reserved.