



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Mini-Power Center

**P48G11S05SS**

**UPC:**786680023835

### Dimensions:

- **Height:** 29.5 IN
- **Length:** 8.9 IN
- **Width:** 11.9 IN

**Weight:**138 LB

**Notes:**Grade 304 stainless steel enclosure

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Mini-power center
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 3RX
- **Frame:** 284
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at -5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 5 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 110A5K

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - P48G11S05SS](#)

### Certifications:

- UL Listed
- ANSI



- CSA Certified
- IEEE Certified

**Product compliance:**

- NEMA Compliant

---

© 2016 Eaton. All rights reserved.