



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General-Purpose Transformer

V24M28T75

UPC:786680036422

### Dimensions:

- **Height:** 39 IN
- **Length:** 22 IN
- **Width:** 29 IN

**Weight:**500 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Dry Type Distribution Transformer
- **Design:** DT-3
- **Coil Material:** Aluminum windings
- **Frame:** 914D
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 240V
- **Secondary Voltage:** 208Y/120V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 75 KVA
- **Weathershield:** WS39

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - V24M28T75](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



