



Powering Business Worldwide

pe.eaton.com

FERRUPS UPS

FE000AA0A0A0A0A

UPC:790341042158

Dimensions:

- **Height:** 15.1 IN
- **Length:** 20.2 IN
- **Width:** 15.2 IN

Weight:102 LB

Warranties:

- 2 year

Specifications:

- **Accessories:** 15A charger
- **Battery Type:** VRLA, standard battery, standard charger
- **Efficiency:** 88% efficiency
- **Humidity:** 5 to 95% non-condensing
- **Input:** Hardwired input
- **Operating Temperature:** 0° to 40°C
- **Output:** Hardwired output
- **Output Voltage:** 120V
- **Topology:** Ferroresonant
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 1400 KVA

Supporting documents:

- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FE000AA0A0A0A0A](#)

Certifications:

- CSA Certified
- ANSI/IEEE Std C62.41
- EN 62040-2
- ANSI/IEEE Std C62.45



- UL Listed
- FCC Cat. A

Product compliance: No Data

© 2016 Eaton. All rights reserved.