



Powering Business Worldwide

pe.eaton.com

Adjustable Frequency Drive

SPX350A1-4A4N1

UPC:782116896004

Dimensions:

- **Height:** 79.45 IN
- **Length:** 23.7 IN
- **Width:** 23.43 IN

Weight:875 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** No brake chopper
- **Input:** Three-phase, EMC L
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR10
- **Horsepower:** 350 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480V

Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SPX350A1-4A4N1](#)
- [Product Datasheet - SPX350A1-4A4N1](#)

Certifications:

- IEC 61800-2
- UL 508C
- UL Listed
- EN 61800-3 Level H

Product compliance: No Data



