



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor

13104RS3162

UPC:782113945170

Dimensions:

- **Height:** .71 IN
- **Length:** 3.02 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Type:** Photoelectric Sensor
- **Contact Rating:** 100 mA PNP, 250 mA NPN at 10-30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN and PNP open collector
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12, 13, IP69k
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Dc Current:** 100 mA PNP, 250 mA NPN
- **Operating Mode:** Background suppression
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset S/C
- **Sensor Type:** Back Ground Suppression
- **Series:** Comet

Supporting documents:

- [Eaton Specification Sheet - 13104RS3162](#)

Certifications: No Data

Product compliance: No Data



