



Powering Business Worldwide

pe.eaton.com

E57 Premium+ Series Tubular Inductive Proximity Sensor

E57LAL18T111E4

UPC:782113988238

Dimensions:

- **Height:** 2.6 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight: .375 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 3%
- **Connection:** 13.1 Ft. (4m) Cable
- **Contact Rating:** 500 mA at 6-30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** Normally Open PNP
Open Collector
- **Cord Length:** 157.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** IP67, IP69K, UL Type 1, NEMA 6P, 4X
- **Input Voltage:** 6–48 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL18T111E4](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.