



Powering Business Worldwide

pe.eaton.com

SLX9000 Micro Drive

SLX007A2-4A1B0

UPC:782116928897

Dimensions:

- **Height:** 8.4 IN
- **Length:** 5.6 IN
- **Width:** 16.5 IN

Weight:17.9 LB

Notes:230V drives up to 15 hp and 480V drives up to 30 hp are only available with brake chopper option B. All others come with brake chopper option N as standard. No standard boards

Warranties:

- 2 year

Specifications:

- **Enclosure:** NEMA 12
- **Frame Size:** MF5
- **Horsepower:** 7.5 hp
- **Phase:** Three-phase
- **Special Features:** Alphanumeric keypad, internal brake chopper circuit, standard software
- **Type:** SLX9000
- **Voltage Rating:** 480V, 380-500V

Supporting documents:

- [Eaton's Volume 6-Solid-State Motor Control](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SLX007A2-4A1B0](#)

Certifications:

- IEC 61800-5
- EN 60204-1
- EN 50178
- UL Listed
- cUL Certified



Product compliance:

- GoST-R
- CE Marked
- FI

© 2016 Eaton. All rights reserved.