



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Capacitive Proximity Sensor

E53KBL18T111SD

UPC:782114013052

### Dimensions:

- **Height:** .71 IN
- **Length:** 3.74 IN
- **Width:** .71 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Threaded body
- **Connection:** M12
- **Contact Rating:** 300 mA Solid State Output
- **Contact Configuration:** NC PNP open collector
- **Diameter:** .708661422 MM
- **Enclosure Material:** POM, mounting nuts, nylon PA66
- **Environmental Rating:** NEMA 1, 2, 3, 3S, 4, 12, 13, IP65
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Dc Current:** 300 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C and reverse polarity
- **Series:** E53

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Sensing solutions-versatile, robust and innovative](#)
- [Eaton Specification Sheet - E53KBL18T111SD](#)



**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.