



Powering Business Worldwide

pe.eaton.com

10316 Series Non Plug-In Style Limit Switch

10316ED185

UPC:782113635514

Dimensions:

- **Height:** 2.25 IN
- **Length:** 1.55 IN
- **Width:** 3.88 IN

Weight:1.125 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 0.22A at 125Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 4, 13
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.22A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Side Rotary

Supporting documents:

- [Eaton Specification Sheet - 10316ED185](#)

Certifications: No Data

Product compliance:

- Contact Manufacturer

