



Powering Business Worldwide

pe.eaton.com

DS7 Soft Start Controller

DS7-34DSX032N0-D

UPC:786685856360

Dimensions:

- **Height:** 4.96 IN
- **Length:** 5.6 IN
- **Width:** 1.77 IN

Weight: .9 LB

Notes: No internal radio interference suppression filters

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Bypass:** Internal bypass
- **Circuit Breaker Type:** HFD3070
- **Fuse Size:** 50A class RK5 max
- **Control Voltage:** 24 Vdc
- **Environmental Rating:** IP20
- **Frame Size:** Frame 2
- **Horsepower:** 20 hp
- **Phase:** Three-phase mains supply voltage
- **Rated Operational Current:** 32A
- **Series:** Generation 7
- **Voltage Rating:** 480V
- **Wire Type:** SmartWire-DT

Supporting documents:

- [DS7 Series soft start controller](#)
- [DS7 series soft start controllers, Frame 2 \(16-32A\)](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Eaton Specification Sheet - DS7-34DSX032N0-](#)



D

Certifications:

- IEC 60947-4-2
- EN 60947-4-2
- UL Listed
- CSA Certified

Product compliance:

- C-Tick Compliant
- CE Marked