



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch commercial loadcenter cover

3BR42STNY

UPC:782114801239

### Dimensions:

- **Height:** 44 IN
- **Length:** 18.13 IN
- **Width:** 1.75 IN

**Notes:** Approved for 150A and up for residential services in new york city

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Approved for use in new york
- **Type:** Surface cover for 3BR4242n225ny
- **Box Size:** B
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Galvanized steel
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CC
- **Mounting:** Surface
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Used With:** 3BR4242n225ny
- **Voltage Rating:** 208Y/120 or 240 Vac
- **Wire Size:** #1-300 kcmil Cu/Al at 60°C or 75°C

### Supporting documents:

- [Eatons Volume 1-Residential and Light](#)



Commercial

- Eaton Specification Sheet - 3BR42STNY

**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.