



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## K-Factor Non Linear Transformer, Ventilated

**N48M28T12CU**

**UPC:**786680105340

### Dimensions:

- **Height:** 48.56 IN
- **Length:** 23.42 IN
- **Width:** 28.22 IN

**Weight:**1097 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Electrostatically Shielded
- **Design:** K-13
- **Coil Material:** Copper windings
- **Frame:** 916A
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 208Y/120V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 112.5 KVA
- **Weathershield:** WS19

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - N48M28T12CU](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



