



Powering Business Worldwide

pe.eaton.com

Type PS Precision Limit Switch

10316H119

UPC:782113228716

Dimensions:

- **Height:** 2.81 IN
- **Length:** 2.19 IN
- **Width:** .97 IN

Weight: .1 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 40A MK, 15A BK at 120 Vac, 0.5A MK/BK at 120 Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Zinc Plated Steel
- **Maximum Ac Current:** 40A Make, 15A Break
- **Maximum Dc Current:** 0.5A Make, 0.5A Break
- **Switch Type:** Roller Lever, Top Right

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H119](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- Contact Manufacturer

