



Powering Business Worldwide

pe.eaton.com

AccuProx Series Tubular Analog Output Inductive Proximity Sensor

E59-A30C125D01-C1

UPC:786685104690

Dimensions:

- **Height:** 2.92 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

Weight:.375 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 30um after 1 hour warmup
- **Connection:** 4 Pin M12 Connector
- **Cable Type:** PVC
- **Diameter:** 1.18 IN
- **Enclosure Material:** Tube: Stainless Steel,
End Bell: Polycarbonate, Front Cap:
Polyphenylene Sulfide
- **Environmental Rating:** NEMA
4,4X,6,6P,12,13,IP67,IP69K
- **Input Voltage:** 15-30 Vdc
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -40° to 158°F (-40° to
70°C)
- **Protection:** Reverse polarity and short circuit
- **Sensor Type:** Analog Inductive Proximity
- **Switch Type:** Inductive Proximity

Supporting documents:

- [AccuProx analog sensor](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E59-A30C125D01-C1](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.