



Powering Business Worldwide

pe.eaton.com

SVX Independent Drives

SVX060A1-4A1N1B5

UPC:782116265657

Dimensions:

- **Height:** 24.8 IN
- **Length:** 10.1 IN
- **Width:** 9.3 IN

Weight:77.2 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** No brake chopper
- **Extended Io Card:** 3 RO(NO)
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR7
- **Horsepower:** 60 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480V

Supporting documents:

- [9000X AFD User Manual](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX060A1-4A1N1B5](#)

Certifications:

- UL 508C



- EN 61800-3 Level H
- IEC 61800-2

Product compliance: No Data

© 2016 Eaton. All rights reserved.