



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Solar DC Disconnect

DCG6061URM

UPC:786685557182

### Dimensions:

- **Height:** 10.22 IN
- **Length:** 19.08 IN
- **Width:** 12.88 IN

**Weight:**30 LB

**Notes:**Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** DC disconnect/grounded system
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Configuration:** Non-fusible
- **Ground:** Grounded
- **Main Lug Wire Size:** #14-#2 AWG lug capacity, #14-1/0 AWG solid return
- **Number Of Circuits:** 6 circuits
- **Series:** DC Photovoltaic Applications
- **Voltage Rating:** 600 Vdc
- **Wire Size:** #14-#4 AWG input grd., #14-#4 AWG output grd.

### Supporting documents:

- [DC disconnects for grounded and ungrounded photovoltaic installations](#)



- Eatons Volume 15-Solar Inverters and Electrical Balance of System
- Eaton Specification Sheet - DCG6061URM

**Certifications:**

- UL 98B
- NEC 690 per UL 1741

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.