



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E57 Small Diameter Series Inductive Proximity Sensor

**E57EBL8T111ED**

**UPC:**782113909066

### Dimensions:

- **Height:** 1.97 IN
- **Length:** .31 IN
- **Width:** .31 IN

**Weight:**.05 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 200 mA at 30 Vdc
- **Contact Configuration:** PNP Open Collector, Normally Closed
- **Diameter:** .315 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 200 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57EBL8T111ED](#)

**Certifications:** No Data



**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.