



Powering Business Worldwide

pe.eaton.com

Series G, EG-frame Molded Case Circuit Breaker

EGE3100FFGV

UPC:782116147298

Dimensions:

- **Height:** 5.5 IN
- **Length:** 2.99 IN
- **Width:** 3 IN

Weight:3 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 100A
- **Interrupt Rating:** 35 kAIC at 240V, 25 kAIC at 415V, 25 kAIC at 480V, 18 kAIC at 600Y/347V
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600Y/347V
- **Mounting Hardware:** Metric
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Line and load
- **Trip Type:** Fixed thermal, fixed magnetic
- **Calibration:** 50°C

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - EGE3100FFGV](#)

Certifications:

- CSA Certified
- IEC Rated
- UL Listed



Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.