



Powering Business Worldwide

pe.eaton.com

Continuous Duty AC Solenoid

10370H25

UPC:782113236056

Dimensions:

- **Height:** 3.63 IN
- **Length:** 2.25 IN
- **Width:** 2.38 IN

Notes: Mounting of solenoids “with conduit box”—Size A are for wall mounting—Size B, C and D are for floor mounting.

Warranties:

- 1 year

Specifications:

- **Magnetic Force Against Gravity:** 0.55 lbs at 100% voltage, 0.33 lbs at 85% voltage
- **Magnetic Force Horizontal:** 0.72 lbs at 100% voltage, 0.50 lbs at 85% voltage
- **Magnetic Force With Gravity:** 0.90 lbs at 100% voltage, 0.68 lbs at 85% voltage
- **Frequency Rating:** 60 Hz
- **Full Load Current Range:** Inrush .92A/Sealed .17A
- **Mounting:** Wall mount
- **Operation:** Push type
- **Size:** A

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 10370H25](#)

Certifications: No Data

Product compliance: No Data

