



Powering Business Worldwide

pe.eaton.com

NEMA Modular Universal Mounting Terminal Block

TBU12

UPC:786678208152

Dimensions:

- Height: X
- Length: X
- Width: X

Notes:Based on 50 degrees C rise, test at 25 degrees C ambient while using maximum wire size. Must be ordered in standard package quantity or in multiples of these quantities. 60 AMP with crimped wire.

Warranties:

- 1 year

Specifications:

- Type: TB
- Amperage Rating: 50A
- Enclosure: NEMA
- Maximum Wire Size: #8 AWG
- Mounting: Base
- Number Of Poles: 12-pole
- Voltage Rating: 600V

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - TBU12](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



