



Powering Business Worldwide

pe.eaton.com

CN35 or A202 Enclosed Lighting Contactor

ECL03B1A9A-S3

UPC:786685357904

Dimensions:

- **Height:** 15.875 IN
- **Length:** 14.625 IN
- **Width:** 8.375 IN

Weight:15.5 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Accessories:** HAND/OFF/AUTO selector switch
- **Amperage Rating:** 20A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Nine-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Eaton's Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03B1A9A-S3](#)

Certifications:

- cUL Listed
- UL Listed

Product compliance: No Data



