



Powering Business Worldwide

pe.eaton.com

30.5 mm, Class I Division 2 Assembled Control Station

10250T7033P

UPC:782114518496

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Actuator:** 1 indicating light, 2 PBs, 1 flush, 1 extended
- **Actuator Color:** Red, black
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Polyester
- **Legend:** START STOP
- **Light Unit Type:** Transformer
- **Light Unit Voltage:** 120 Vac
- **Number Of Elements:** 3
- **Operating Mode:** Momentary
- **Rating:** NEMA 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T7033P](#)

Certifications: No Data

Product compliance: No Data



