



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Thermal-Magnetic Circuit Breaker

**BAB3025C**

**UPC:**786679391303

### Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.8 IN
- **Width:** 3.2 IN

**Weight:**1.1 LB

**Notes:**HACR rated

### Warranties:

- 1 year

### Specifications:

- **Type:** Quicklag
- **Special Features:** Switching Neutral
- **Amperage Rating:** 25A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** BAB
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on
- **Quantity:** 8

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3025C](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data



