



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Contactor

C25ENF4401T

UPC:782114648407

Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.38 IN
- **Width:** 2.98 IN

Weight:2.3 LB

Notes:Resitive Load rating per pole

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 40A
- **Coil:** 24 Vdc
- **Contact Configuration:** 1NC
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 25-40A, four-pole
- **Model:** Contactor
- **Number Of Poles:** Four-pole
- **Resistive Load:** 50A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25ENF4_1 3D Inventor](#)
- [Eaton Specification Sheet - C25ENF4401T](#)
- [C25ENF4_1 AutoCAD 2D Footprint \(mm\)](#)
- [C25ENF4_1 2D Drawing Xchange](#)
- [C25ENF4_1 AutoCAD 2D Footprint](#)
- [C25ENF4_1 3D Model Xchange](#)
- [C25ENF4_1 2D PDF](#)



Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.