



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Enhanced 50 Series Photoelectric Sensor

1450E-6543

UPC:782116111077

### Dimensions:

- **Height:** 4.01 IN
- **Length:** 1.91 IN
- **Width:** 1.81 IN

**Weight:** .3375 LB

### Warranties:

- 3 year

### Specifications:

- **Connection:** 4 Pin Dual Key Micro Connector
- **Contact Rating:** 300 mA at 240 Vac/Vdc
- **Contact Configuration:** Isolated Solid State Relay
- **Enclosure Material:** Fiberglass reinforced plastic
- **Environmental Rating:** IP 67, IP69K
- **Input Voltage:** 12–240 Vdc 24–240 Vac
- **Led Indicators:** Yellow power on, Green outout status, red marginal gain
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Non Polarized Retroreflective
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Reverse polarity, short circuit and overload
- **Sensor Type:** Retroreflective
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1450E-6543](#)

**Certifications:** No Data



**Product compliance:**

- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.