



Powering Business Worldwide

pe.eaton.com

SM Series Rectangular Body Photoelectric Sensor

E65-SMPP100-HLD

UPC:782114786482

Dimensions:

- **Height:** 1.29 IN
- **Length:** 2.17 IN
- **Width:** 1.47 IN

Weight:.0688 LB

Notes:Sensor will detect a 90% reflectance card at the Sensing Range; sensor will ignore a 90% reflectance card at the Cutoff Range

Warranties:

- 3 year

Specifications:

- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN and PNP Open Collector
- **Enclosure Material:** Lens: polycarbonate cable jacket: PVC body: Cycloy
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Green power on, red output status, orange marginal gain
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Background Suppression
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Sensor Type:** Back Ground Suppression
- **Switch Type:** Photoelectric

Supporting documents:



- [Eaton's Volume 8-Sensing Solutions](#)
- [Test the Best Photoelectric Sensors: SM Series](#)
- [Eaton Specification Sheet - E65-SMPP100-HLD](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance:

- CE Marked