



Powering Business Worldwide

pe.eaton.com

General-Purpose Transformer

V48M28T49EELS47

UPC:786680033308

Dimensions:

- **Height:** 48.56 IN
- **Length:** 23.42 IN
- **Width:** 28.22 IN

Weight:917 LB

Notes:NEMA TP-1 efficient, Low sound equal to 47 dB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Dry Type Distribution Transformer
- **Design:** DT-3
- **Coil Material:** Aluminum windings
- **Frame:** 916A
- **Frequency Rating:** 60 Hz
- **Modification 1:** Low sound 47 dB
- **Phase:** Three-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 208Y/120V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 150 KVA
- **Weathershield:** WS19

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - V48M28T49EELS47](#)

Certifications:



- UL Listed

Product compliance:

- NEMA TP-1 Compliant

© 2016 Eaton. All rights reserved.