



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57-18GE16-AAB

UPC:782116977055

Dimensions:

- **Height:** .71 IN
- **Length:** 3.58 IN
- **Width:** .71 IN

Weight:.2 LB

Warranties:

- 1 year

Specifications:

- **Type:** E57
- **Accuracy:** <3.0% sensing range
- **Connection:** Dual key micro
- **Contact Rating:** 200 mA at 250V
- **Contact Configuration:** 2-wire AC, NO
- **Enclosure Material:** Nickel plated brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 20-250V
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 200 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** 32° to 104°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-18GE16-AAB](#)

Certifications: No Data

Product compliance: No Data

