



Powering Business Worldwide

pe.eaton.com

C30CN Enclosed Lighting Contactor

ECC04C1T6A

UPC:782116156443

Dimensions:

- **Height:** 14.75 IN
- **Length:** 9.75 IN
- **Width:** 8 IN

Weight:13 LB

Notes: Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 24V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Six-pole
- **Type:** Non-combination mechanically held and magnetically latched

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECC04C1T6A](#)

Certifications:

- cUL Listed
- UL Listed

Product compliance: No Data

