



Powering Business Worldwide

pe.eaton.com

10316 Series, Hazardous Location Limit Switch

10316H2159

UPC:782113452098

Dimensions:

- **Height:** 5.35 IN
- **Length:** 3 IN
- **Width:** 3.08 IN

Weight:1.6813 LB

Notes:Field convertible to CW only or CCW only operation. Use only levers with Nylatron rods or rollers with explosion-proof limit switches. Contact factory for availability of CSA &CE approval status.

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 5A at 600Vac, 0.1A at 120Vdc
- **Contact Configuration:** 2NO
- **Enclosure Material:** Cast Bronze
- **Environmental Rating:** NEMA 7 Division I Class I BCD, NEMA 9 Division I Class II EFG, NEMA 1, 4, 4X, 13
- **Maximum Ac Current:** 5A
- **Maximum Dc Current:** 0.1A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Side Rotary

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H2159](#)

Certifications:

- UL Listed
- CSA Certified



Product compliance:

- CE Marked
- Contact Manufacturer

© 2016 Eaton. All rights reserved.