



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series G, EG-frame Molded Case Circuit Breaker

EGB3125FFGV

UPC:782116147137

### Dimensions:

- **Height:** 5.5 IN
- **Length:** 2.99 IN
- **Width:** 3 IN

**Weight:**3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 125A
- **Interrupt Rating:** 25 kAIC at 240V, 18 kAIC at 415V, 18 kAIC at 480V
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600Y/347V
- **Calibration:** 50°C
- **Mounting Hardware:** Metric
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Line and load
- **Trip Type:** Fixed thermal, fixed magnetic

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - EGB3125FFGV](#)

### Certifications:

- IEC Rated
- CSA Certified
- UL Listed



**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.