



Powering Business Worldwide

pe.eaton.com

Type FB Tri-Pac Thermal-Magnetic Circuit Breaker

FB3015PL

UPC:786679765487

Dimensions:

- **Height:** 4.125 IN
- **Length:** 8.75 IN
- **Width:** 3.5 IN

Weight:11.5 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 15A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 100 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Accessories:** Replaceable current limiter
- **Terminals:** Line and load

Supporting documents:

- [Miniature and Molded Case Circuit Breakers](#)
- [Eaton Specification Sheet - FB3015PL](#)

Certifications:

- UL 489

Product compliance: No Data

