



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Premium+ Inductive Proximity Sensor

E57LBL30T111SD

UPC:782113604640

### Dimensions:

- **Height:** 1.18 IN
- **Length:** 2.92 IN
- **Width:** 1.18 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Premium+ Inductive Proximity Sensor
- **Accuracy:** <1% sensing range
- **Connection:** M12
- **Contact Rating:** 500 mA at 6-30 Vdc
- **Contact Configuration:** NC PNP open collector
- **Diameter:** 1.18110237 MM
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** 360° viewable LED
- **Maximum Dc Current:** 500 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Auto reset
- **Series:** E57

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LBL30T111SD](#)

### Certifications:



- CSA Certified
- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.