



Powering Business Worldwide

pe.eaton.com

iProx Sensor

E59-M12C110C02-A1

UPC:782116183234

Dimensions:

- **Height:** .47 IN
- **Length:** 2.46 IN
- **Width:** .47 IN

Weight:1 LB

Warranties:

- 1 year

Specifications:

- **Type:** E59
- **Accuracy:** <3% sensing range
- **Contact Rating:** 200 mA at 20-132 V
- **Size:** 12 mm
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC, NO
- **Cord Length:** 79.2 FT
- **Diameter:** .472440948 MM
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 20-132V
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 200 mA
- **Number Of Wires:** 2-wire
- **Operating Mode:** Unshielded
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Temperature Rating:** -40° to 158°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [iProx sensors](#)
- [Eaton Specification Sheet - E59-M12C110C02-](#)



A1

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.