



Powering Business Worldwide

pe.eaton.com

CurrentWatch Series Current Switch

ECSTD408SP

UPC:786685121130

Dimensions:

- **Height:** 3.53 IN
- **Length:** 2.25 IN
- **Width:** 1.19 IN

Weight: .25 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 0.15A at 240V AC/DC
- **Contact Configuration:** Isolated Solid State Relay
- **Enclosure Material:** UL94 V0 Flammability Rated Plastic
- **Led Indicators:** Red LED for contact status
- **Maximum Ac Current:** Monitor up to 200A, Switch up to 0.2A
- **Operating Temperature:** 5° to 122°F (-15° to 50°C)
- **Switch Type:** Current Switch

Supporting documents:

- [CurrentWatch current sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - ECSTD408SP](#)

Certifications: No Data

Product compliance: No Data

