



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Comet Series Tubular Photoelectric Sensor

13104R6515

UPC:782114290583

### Dimensions:

- **Height:** 3.02 IN
- **Length:** .6 IN
- **Width:** .71 IN

**Weight:** .2875 LB

**Notes:** Sensor will detect a 90% reflectance card at the Sensing Range; sensor will ignore a 90% reflectance card at the Cutoff Range

### Warranties:

- 3 year

### Specifications:

- **Connection:** 6.6 Ft. ( 2m ) Cable
- **Contact Rating:** 300 mA at 90-132 Vac/18-50 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2 Wire AC/DC
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate  
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 90-132 Vac/18-50 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Background Suppression
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Auto reset short circuit



- **Sensor Type:** Back Ground Suppression
- **Switch Type:** Photoelectric

**Supporting documents:**

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 13104R6515](#)

**Certifications:**

- cUL Recognized
- UL Recognized

**Product compliance:**

- CE Marked
- Contact Manufacturer