



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0150E4H

UPC:786680005039

Dimensions:

- **Height:** 3.189 IN
- **Length:** 4.016 IN
- **Width:** 3.74 IN

Weight:6.5 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Primary Voltage:** 380/400/415V
- **Secondary Voltage:** 22/23/24V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 150 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - C0150E4H](#)

Certifications:

- CSA Certified
- cUL Certified



- UL Listed

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.