



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH262FRK

UPC:786685177137

Dimensions:

- **Height:** 16.27 IN
- **Length:** 17 IN
- **Width:** 9.5 IN

Weight:18 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Two-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20 at 480 Vac TD 1 Ph, 25 at 600 Vac TD 1 Ph, 25 at 600 Vdc

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH262FRK](#)

Certifications:

- UL Listed

Product compliance: No Data



