



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Meter Breaker Commercial Safety Sockets

CH217MTBLB

UPC:782116164936

### Dimensions:

- **Height:** 6 IN
- **Length:** 40 IN
- **Width:** 16 IN

**Weight:**38 LB

**Notes:**Order plug-on Type BR, BRH or BRHH circuit breaker separately.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 125A
- **Feed Type:** Overhead
- **Number Of Jaws:** Seven-jaw
- **Phase:** Three-phase
- **Interrupt Rating:** Type BR=10 kAIC, Type BRH=22 kAIC, Type BRHH=42 kAIC
- **Main Circuit Breaker:** Provisions
- **Number Of Wires:** Four-wire
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 208/120V
- **Wire Size:** #14-2/0 AWG

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CH217MTBLB](#)

### Certifications:



- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.