



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH423FDK

UPC:782113206356

Dimensions:

- **Height:** 24.95 IN
- **Length:** 10.22 IN
- **Width:** 15.1 IN

Notes: Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Four-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 7.5 at 240 Vac Std. 1 Ph, 15 at 240 Vac Std. 3 Ph, 15 at 240 Vac TD 1 Ph, 30 at 240 Vac TD 3 Ph, 20 at 250 Vdc

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH423FDK](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.