



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Class I Division 2 Pushbutton Operator

10250T411H

UPC:782114510759

### Dimensions:

- Height: X
- Length: X
- Width: X

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Led Lamp Number:** #755
- **Light Unit Type:** Incandescent, transformer
- **Light Unit Voltage:** 120 Vac
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T411H](#)

### Certifications:

- UL 505
- CSA Certified

### Product compliance:

- CE Marked



