



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## XT IEC Line Metallic Enclosed Control

**ECX09G1AAA-MS29**

**UPC:**786685237688

### Dimensions:

- **Height:** 5.98 IN
- **Length:** 10.01 IN
- **Width:** 6 IN

**Weight:**5.2 LB

**Notes:**Convert contactor or starter from three-phase to single-phase-install jumper

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Voltage:** 120V
- **Enclosure:** NEMA 1
- **Type:** Non-combination non-reversing starter
- **Amperage Rating:** 25A
- **Actuator:** ON/OFF selector switch
- **Degree Of Protection:** IP23
- **Overload Range:** 16-24A
- **Overload Relay:** XTOB: 16-24 FLA
- **Phase:** Single-phase
- **Special Features:** Convert contactor or starter from three-phase to single-phase install jumper

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECX09G1AAA-MS29](#)

### Certifications:

- UL Listed



- cUL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.