



Powering Business Worldwide

pe.eaton.com

Type C361 Flange Mounted Disconnect Switch

C361FND1

UPC:782113752099

Dimensions:

- **Height:** 8.63 IN
- **Length:** 11.38 IN
- **Width:** 6.5 IN

Notes:Maximum horsepower ratings refer to switch only

Warranties:

- 1 year

Specifications:

- **Type:** Switch and operating mechanism with handle
- **Amperage Rating:** 60A
- **Depth Range:** 6.5 in minimum
- **Enclosure:** NEMA 1 or 12
- **Fuse Clip Rating:** Non-fusible
- **Handle Length:** 4 IN
- **Max Hp Rating:** 15 hp at 208 Vac, 15 hp at 240 Vac, 30 hp at 480 Vac, 50 hp at 600 Vac, 10 hp at 250 Vdc
- **Mounting:** Right-hand
- **Wire Size:** #2-14 AWG Cu/Al

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - C361FND1](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



