



Powering Business Worldwide

pe.eaton.com

SLX9000 Micro Drive

SLX020A1-4A1B0

UPC:782116929054

Dimensions:

- **Height:** 9.3 IN
- **Length:** 7.6 IN
- **Width:** 22 IN

Weight:40.8 LB

Notes:230V drives up to 15 hp and 480V drives up to 30 hp are only available with brake chopper option B. All others come with brake chopper option N as standard. No standard boards

Warranties:

- 2 year

Specifications:

- **Enclosure:** NEMA 1
- **Frame Size:** MF6
- **Horsepower:** 20 hp
- **Phase:** Three-phase
- **Special Features:** Alphanumeric keypad, internal brake chopper circuit, standard software
- **Type:** SLX9000
- **Voltage Rating:** 480V, 380-500V

Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SLX020A1-4A1B0](#)

Certifications:

- cUL Certified
- EN 60204-1
- EN 50178
- UL Listed
- IEC 61800-5



Product compliance:

- CE Marked
- FI
- GoST-R

© 2016 Eaton. All rights reserved.