



Powering Business Worldwide

pe.eaton.com

Mini Complete Limit Switch

E49G31BP3

UPC:786685102061

Dimensions:

- **Height:** .98 IN
- **Length:** 3.9 IN
- **Width:** 1.1 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 5A at 250 Vac, 5A at 30 Vdc
- **Actuator:** Top pushbutton
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Cast zinc
- **Environmental Rating:** IP65
- **Maximum Ac Current:** 5A continuous
- **Maximum Dc Current:** 5A at 30 Vdc
- **Operating Speed:** 5 mm-50 cm/s
- **Operating Temperature:** 23° to 149°F (-5° to 65°C)
- **Series:** E49

Supporting documents:

- [E49 Mini Metal Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E49G31BP3](#)

Certifications: No Data

Product compliance: No Data

