



Powering Business Worldwide

pe.eaton.com

Intelliview Photoelectric Sensor

E75-PP1MP-M12

UPC:786685262420

Dimensions:

- **Height:** 2.6 IN
- **Length:** 1.97 IN
- **Width:** .9 IN

Warranties:

- 3 year

Specifications:

- **Connection:** M12
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Contact Configuration:** Complementary PNP open collector
- **Enclosure Material:** ABS
- **Environmental Rating:** IP67
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output (yellow), stability (green)
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Background suppression
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Sensor Type:** Back Ground Suppression
- **Series:** E75

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Introducing IntelliView](#)
- [Eaton Specification Sheet - E75-PP1MP-M12](#)

Certifications: No Data

Product compliance: No Data



