



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Inductive Proximity Sensor

E56ADL50UAD01

UPC:786685197234

### Dimensions:

- **Height:** 1.54 IN
- **Length:** 4.32 IN
- **Width:** 3.13 IN

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** <3%
- **Connection:** M12
- **Contact Rating:** 300 mA
- **Contact Configuration:** Complementary NPN/PNP auto-configure
- **Enclosure Material:** PPS housing
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67
- **Input Voltage:** 10-42 Vdc
- **Led Indicators:** Power (green), output status (red)
- **Number Of Pins:** 4 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C with auto-reset
- **Series:** E56

### Supporting documents:

- [E52Q Cube and E56 Pancake inductive sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E56ADL50UAD01](#)

**Certifications:** No Data

**Product compliance:** No Data



