



Powering Business Worldwide

pe.eaton.com

CE Marked Control Transformer

CE0500K2UCEFS

UPC:786680042034

Dimensions:

- **Height:** 5.079 IN
- **Length:** 6.181 IN
- **Width:** 5.236 IN

Weight:20.5 LB

Notes:Epoxy resin impregnated coil design, 50/60 Hz operation, 180°C insulation system

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTK
- **Modification 1:** Factory-mounted finger-safe terminal shields
- **Primary Voltage:** 220/380/440/550V, 230/400/460/575V, 240/416/480/600V
- **Secondary Voltage:** 23/110V, 24/115V, 25/120V
- **Tap Size:** None
- **Temperature Rating:** 115°C
- **Type:** CE Marked Control Transformer
- **Volt Ampere Rating:** 500 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - CE0500K2UCEFS](#)

Certifications:

- UL Listed



- IEC 61558-2
- CSA Certified
- cUL Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.