



Powering Business Worldwide

pe.eaton.com

FERRUPS UPS

FH010AA0A0A0A0B

UPC:743172067081

Dimensions:

- **Height:** 21.2 IN
- **Length:** 22.9 IN
- **Width:** 15.25 IN

Weight:248 LB

Warranties:

- 2 year

Specifications:

- **Efficiency:** 91% efficiency
- **Humidity:** 5 to 95% non-condensing
- **Input:** Hardwired
- **Operating Temperature:** 0° to 40°C
- **Topology:** Ferroresonant
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 3100 KVA
- **Cable Type:** Communication cable
- **Color:** Beige with blue highlights
- **Configuration:** Tower
- **Runtime:** 14 min full load, 35 min half load
- **Serial Interface:** RS-232 serial port, DB25, plus contact closures
- **Software:** LanSafe, PowerVision, Foreseer
- **Wattage:** 2.2kW

Supporting documents:

- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FH010AA0A0A0A0B](#)

Certifications:

- IEC 801-2



- IEC 801-4
- IEC 801-5
- UL Listed
- ANSI/IEEE Std C62.41
- ANSI/IEEE Std C62.45
- CSA Certified
- FCC Cat. A

Product compliance: No Data

© 2016 Eaton. All rights reserved.